FFOOAdSZauk

Atacmama Atabites 7.5Kg x 2 (25 GBP)



Location South East, East Sussex https://www.freeadsz.co.uk/x-406316-z



In order to get the best possible sound from your speaker stands, it is reccomended that the main columns are filled with a high density inert filler. This will reduce ringing and give a sonically dead platform from which to position bookshelf style speakers. By adjusting the amount of filler used, you can experiment to find the optimum amount of filler to suit your speakers .Featuring new zinc coated microdiscs, the NEW UPGRADED Atabite inert filler now gives increased density to volume over the old Atabite inert filler and has a uniformed particulate size giving consistant sonic performance. The Zinc coating reduces any oxidisation and degradation and enhances the visual aesthetics. PLEASE NOTE-Atabites are supplied by weight, not volume. (7.5 KG tubs). Some settling of contents may occur in transit. Here is the maximum Approximate weight of Atabites that can be used in each pair of speaker stands:- Moseco 6 Duo 6=10.4KG Moseco 7 Duo 7=12.2Kg Moseco 10 21KG, Duo 10=N/A Nexus 6i=8.2KG Nexus7i=12.2KG Nexus10i=21KG SL200=7.2KG SL300=15.2KG SL400=24KG SL500=32.8KG SL600=41.6KG SL700=48.8KG SL1000=68KG HMS1.1 500mm=34KG HMS1.1 600mm=41.8KG HMS1.1 700mm=55.4KG HMS2.1=84KG. Sonic results will depend on speaker stand positioning, type of speaker, room size, type of electronics and cabling, listening position and personal taste. However, as a general rule filling the stands approximately two thirds full generally gives the best results. NOT suitable for Aurora 6 Speaker stands. I have x 2 of these to sell @ 25.00

